



Healthcare  
Solutions


## High Consistency Rubber

*Application and Product Selection Guide*

# Proven Performance. Trusted Expertise.



Advancing healthcare through  
**material innovations**



# High Consistency Rubber (HCR)

HCRs are millable thermoset silicone elastomers that can be extruded continuously to form a desired size and shape before curing. Silicone tubing is an example.

## Innovation Meets Expertise

You want to explore new directions and create the next generation of medical device technology. You have a powerful ally with Dow Corning. When we are part of your team, you're backed by our expertise and our culture of discovery and innovation, which has been nurtured by six decades of proven performance. You'll find a depth of knowledge not just in silicone chemistry, but in the medical device industry, process technology and regulatory compliance.

Benefits	Product Description	Typical Applications
<b>HCR</b>		
<p><b>Silastic® BioMedical Grade Elastomers</b></p> <ul style="list-style-type: none"> <li>DMF (drug master file) access available upon request for select <i>Silastic®</i> brand BioMedical Grade materials</li> </ul>	<ul style="list-style-type: none"> <li>Excellent batch-to-batch reproducibility for critical applications</li> <li>Manufactured in a dedicated healthcare facility</li> </ul>	<p>Two-part (1:1 by weight), platinum-catalyzed, enhanced tear-resistance silicone elastomers</p>
<p><b>Silastic® BioMedical Grade Bases</b></p> <ul style="list-style-type: none"> <li>DMF (drug master file) access available upon request for select <i>Silastic</i> BioMedical Grade materials</li> <li>Must add peroxide</li> </ul>		<ul style="list-style-type: none"> <li>Fabrication of extruded parts</li> <li>Fabrication of molded medical/surgical/diagnostic devices and components</li> </ul>
<b>Dow Corning® C6 Series Elastomers</b>		
<p><b>Dow Corning® C6 Series Elastomers</b></p> <ul style="list-style-type: none"> <li>Must add peroxide</li> </ul>	<ul style="list-style-type: none"> <li>Highly reproducible and stable materials</li> <li>Manufactured in a dedicated healthcare facility</li> <li>Improved cost efficiency</li> </ul>	<p>Two-part (1:1 by weight), platinum-catalyzed, enhanced tear-resistance silicone elastomers</p>
<p><b>Dow Corning® C6 Series Elastomers</b></p> <ul style="list-style-type: none"> <li>Must add peroxide</li> </ul>		<p>One-part, high-consistency rubber base</p>
<b>Dow Corning® QP1 Elastomers</b>		
<p><b>Dow Corning® QP1 Elastomers</b></p> <ul style="list-style-type: none"> <li>Base, must add curatives</li> </ul>	<ul style="list-style-type: none"> <li>Choice of cure systems (peroxide/platinum)</li> <li>Manufactured under ISO quality system requirements</li> </ul>	<p>One-part, high-consistency rubber base</p>
<b>Dow Corning® C6 Series Elastomers</b>		
<p><b>Dow Corning® C6 Series Elastomers</b></p> <ul style="list-style-type: none"> <li>Low hysteresis</li> </ul>	<ul style="list-style-type: none"> <li>Lower hysteresis for demanding applications (i.e. peristaltic pump tubing)</li> </ul>	<p>Two-part (1:1 by weight), platinum-catalyzed, enhanced tear-resistance silicone elastomers</p>
<ul style="list-style-type: none"> <li>Fabrication of extruded parts</li> <li>Fabrication of molded medical/surgical/diagnostic devices and components</li> </ul>		

## Products


	Biocompatibility Testing									Select European Pharmacopeia 3.1.9		Food Grade Compliance*	Hardness, Shore A	Tensile Strength (MPa/psi)	Elongation at Break (%)	Tear Strength, Die B (kN/m/ppi)	Relative Density	
	Cytotoxicity	Mutagenicity/Genotoxicity	Hemolysis	Skin Sensitization	Pyrogenicity (USP)	90-Day Implant	30-Day Implant	7-Day Implant	USP Class V and VI	Substance Soluble in Hexane	Volatile Matter							
<i>Silastic</i> ® Q7-4720 BioMedical Grade ETR Elastomer <sup>1</sup>	•	•	•	•	•	•	•	•	•	•	•	•	23	8.9/1300	1310	31.6/180	1.11	
<i>Silastic</i> ® Q7-4735 BioMedical Grade ETR Elastomer <sup>1</sup>	•	•	•	•	•	•	•	•	•	•	•	•	36	9.3/1350	1180	36.8/210	1.12	
<i>Silastic</i> ® Q7-4750 BioMedical Grade ETR Elastomer <sup>1</sup>	•	•	•	•	•	•	•	•	•	•	•	•	50	10.0/1450	930	45.6/260	1.16	
<i>Silastic</i> ® Q7-4765 BioMedical Grade ETR Elastomer <sup>1</sup>	•	•	•	•	•	•	•	•	•	•	•	•	65	8.0/1160	900	45.6/260	1.20	
<i>Silastic</i> ® Q7-4780 BioMedical Grade ETR Elastomer <sup>1</sup>	•	•	•	•	•	•	•	•	•	•	•	•	77	7.8/1130	660	42.1/240	1.20	
<i>Silastic</i> ® Q7-4535 BioMedical Grade ETR Elastomer <sup>1,2</sup>	•	•	•	•	•	•	•	•	•	•	•	•	36	8.1/1180	830	24.6/140	1.12	
<i>Silastic</i> ® Q7-4550 BioMedical Grade ETR Elastomer <sup>1,2</sup>	•	•	•	•	•	•	•	•	•	•	•	•	48	9.3/1360	680	31.6/180	1.16	
<i>Silastic</i> ® Q7-4565 BioMedical Grade ETR Elastomer <sup>1,2</sup>	•	•	•	•	•	•	•	•	•	•	•	•	67	7.9/1150	620	38.6/220	1.20	
<i>Dow Corning</i> ® C6-135 Elastomer	•			•			•	•	•	•	•	•	36	8.2/1200	1120	35.1/200	1.12	
<i>Dow Corning</i> ® C6-150 Elastomer	•			•			•	•	•	•	•	•	50	10.6/1540	980	42.1/240	1.16	
<i>Dow Corning</i> ® C6-165 Elastomer	•			•			•	•	•	•	•	•	61	8.0/1170	940	42.1/240	1.21	
<i>Dow Corning</i> ® C6-180 Elastomer	•			•			•	•	•	•	•	•	77	7.2/1050	610	38.6/220	1.21	
<i>Dow Corning</i> ® C6-235 Elastomer <sup>2</sup>	•			•			•	•	•	•	•	•	37	7.5/1100	810	21.1/120	1.12	
<i>Dow Corning</i> ® C6-250 Elastomer <sup>2</sup>	•			•			•	•	•	•	•	•	49	8.2/1200	530	26.3/150	1.16	
<i>Dow Corning</i> ® C6-265 Elastomer <sup>2</sup>	•			•			•	•	•	•	•	•	66	8.2/1200	560	35.1/200	1.20	
<i>Dow Corning</i> ® QP1-30 Silicone Elastomer <sup>3</sup>	•							•	•				•	28	9.5/1390	790	12.3/70	1.09
<i>Dow Corning</i> ® QP1-50 Silicone Elastomer <sup>3</sup>	•							•	•				•	48	11.8/1720	545	15.8/90	1.13
<i>Dow Corning</i> ® QP1-60 Silicone Elastomer <sup>3</sup>	•							•	•				•	57	13.0/1890	535	21.1/120	1.16
<i>Dow Corning</i> ® QP1-70 Silicone Elastomer <sup>3</sup>	•							•	•				•	68	12.6/1835	470	24.6/140	1.20
<i>Dow Corning</i> ® C6-350 LH Elastomer	•			•			•	•	•	•	•	•	•	49	8.5/1240	730	38.6/220	1.15

<sup>1</sup> Use of this material for implantation ≥ 30 days requires indemnification

<sup>2</sup> 1.0 parts Di(2,4-Dichlorobenzoyl) peroxide compounded with 100 parts base molded 5 min at 115 °C (240 °F)

<sup>3</sup> 1.2 parts Di(2,4-Dichlorobenzoyl) peroxide compounded with 100 parts base molded 5 min at 115 °C (240 °F)

\* Contact your Dow Corning representative for area-specific information



## Contact Dow Corning

When you need innovation, Dow Corning can help. We are dedicated to meeting your needs for specialty materials, collaborative problem solving and innovation support. We have state-of-the-art application center laboratories in our facilities. Learn how we can help you at [dowcorning.com/healthcare](http://dowcorning.com/healthcare).

## Your Global Connection

Dow Corning has sales offices and manufacturing facilities worldwide, as well as full-service, global technical support. Contact us today by visiting [dowcorning.com/ContactUs](http://dowcorning.com/ContactUs).

Images: AV19601, AV24405, AV03454, AV18540, AV02278, AV19192

### LIMITED WARRANTY INFORMATION - PLEASE READ CAREFULLY

The information contained herein is offered in good faith and is believed to be accurate. However, because conditions and methods of use of our products are beyond our control, this information should not be used in substitution for customer's tests to ensure that our products are safe, effective and fully satisfactory for the intended end use. Suggestions of use shall not be taken as inducements to infringe any patent.

Dow Corning's sole warranty is that our products will meet the sales specifications in effect at the time of shipment.

Your exclusive remedy for breach of such warranty is limited to refund of purchase price or replacement of any product shown to be other than as warranted.

**TO THE FULLEST EXTENT PERMITTED BY APPLICABLE LAW, DOW CORNING SPECIFICALLY DISCLAIMS ANY OTHER EXPRESS OR IMPLIED WARRANTY OF FITNESS FOR A PARTICULAR PURPOSE OR MERCHANTABILITY.**

**DOW CORNING DISCLAIMS LIABILITY FOR ANY INCIDENTAL OR CONSEQUENTIAL DAMAGES.**

®™ Trademark of The Dow Chemical Company ("Dow") or an affiliated company of Dow. Dow Corning is a registered trademark of Dow Corning Corporation. The Corning portion of the Dow Corning trademark is a trademark of Corning Incorporated, used under license.

© 2014-2017 Dow Corning Corporation, a wholly owned subsidiary of The Dow Chemical Company. All rights reserved.

30024738

Form No. 52-1225B-01 Insert A

