



Versaflex™ HC Thermoplastic Elastomers (TPEs) HAI Prevention Has an Ally

Don't let your medical devices fall victim to aggressive disinfectant protocols.

Are your medical devices delaminating, cracking or losing their resilience after exposure to more frequent hospital disinfection aimed at reducing Hospital Acquired Infections (HAIs)? Your devices now have a new ally with Versaflex™ HC TPEs (thermoplastic elastomer) for medical overmolding.

These TPE material options can help you create long-lasting products that resist disinfectants used to advance patient safety. PolyOne has developed these specialty materials to resist the disinfectants used in HAI prevention

while improving the useful life and tactile performance of medical devices.

Versaflex HC TPE for overmolded medical devices offers enhanced resistance to commonly used disinfectants and antiseptic cleaners. Our new TPEs also enhance ergonomics by adding a soft touch and improved grip. Designed for two-shot injection molding, the materials are compatible with rigid PVC, copolyesters, all PC alloys, ABS, TPUs and PEI substrates. Typical applications include device housings for hand-held scanners, patient monitors, infusion pumps, defibrillators, reusable surgical devices and other durable medical products.

VERSAFLEX HC TPES FOR OVERMOLDED MEDICAL DEVICES PROVIDE:

- Resistance to common disinfectants and other chemicals
- Excellent bonding to engineering thermoplastics
- Customization in molding to achieve desired haptics (touch and feel)
- USP VI & ISO10993 rated solutions
- Ergonomic design freedom



AVERAGE PEEL STRENGTH

Substrate	Versaflex™ HC 1348	Versaflex™ HC 1365	Versaflex™ OM 1040X	Versaflex™ OM 3060
PC	12-20	12-20	12	15
PC/ABS	15-18	15-20	12-15	12-18
PC/PET	15	13-20	ND	ND
ABS	17-25	17-25	14	10-15
COPE	15	12-17	13	12-15
PP	NA	NA	13	14-18

Notes: NA=No adhesion to <10pli, ND=No Data

Properties shown are typical values and are not intended as product specifications. All properties were measured using natural product unless otherwise specified. For some products, the black properties will differ slightly from the natural version—refer to product Technical Data Sheet for specific product properties. The test methods used are modifications of the ASTM/ISO procedures—refer to product Technical Data Sheet for specific testing parameters. All tests are conducted on injection molded samples.

* Please refer to technical data sheet for complete information.

1-866-POLYONE
www.polyone.com

PolyOne™

Copyright © 2016, PolyOne Corporation. PolyOne makes no representations, guarantees, or warranties of any kind with respect to the information contained in this document about its accuracy, suitability for particular applications, or the results obtained or obtainable using the information. Some of the information arises from laboratory work with small-scale equipment which may not provide a reliable indication of performance or properties obtained or obtainable on larger-scale equipment. Values reported as "typical" or stated without a range do not state minimum or maximum properties; consult your sales representative for property ranges and min/max specifications. Processing conditions can cause material properties to shift from the values stated in the information. PolyOne makes no warranties or guarantees respecting suitability of either PolyOne's products or the information for your process or end-use application. You have the responsibility to conduct full-scale end-product performance testing to determine suitability in your application, and you assume all risk and liability arising from your use of the information and/or use or handling of any product. POLYONE MAKES NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, either with respect to the information or products reflected by the information. This literature shall NOT operate as permission, recommendation, or inducement to practice any patented invention without permission of the patent owner.